



german|engineering

IPL
VELVET SKIN PRO

beurer
beauty

IPL VELVET SKIN PRO

Long-lasting hair removal



Free "beurer MyIPL" app guides through the treatment and creates an individual treatment plan - for a professional IPL treatment at home



Up to 300.000 light pulses



Convenient use thanks to cordless design



Skin tone detection - automatically sets the correct energy level

Around just 21 min. to treat the entire body¹⁾

4.5 cm² light surface for especially fast treatment

With useful "Auto-Flash" mode for convenient application

6 different intensity levels

Extra attachment for face and bikini line

Clinically tested technology for maximum safety at home

Maximum safety with 2-in-1 skin-type and skin-contact sensor

Up to 50% hair reduction after 3-4 treatments

State-of-the-art IPL light technology used by dermatologists for professional hair removal.

Deactivates the hair roots deep beneath the skin and in doing so decreases the chance of the hair growing back.

Integrated UV filter to protect the skin

Cannot be used on dark skin

May be ineffective on white or light-coloured hair



Incl. Li ion battery 7.4 V~; 2500 mAh

Product measurements (LxWxH): 200 x 175 x 65 mm

Product weight: approx. 480 g

5 year guarantee

Sales unit: 2 / Shipping carton: -

EAN no.: 4211125 57513 7

Item no.: 575.13



0617 Subject to errors and changes

* Dermatological study, 20 women, Institut proDERM Hamburg, study no. 14.0309-11

¹⁾ at minimum power level for arms, legs, face, armpits and the bikini line




german|engineering


IPL
VELVET SKIN PRO

beurer
beauty


MODE OF ACTION



Melanin in the hair
absorbs the light (IPL)




The warmth generated
deactivates the hair follicle



The hair falls out and does
not continue to grow

HAIR AND SKIN COLOUR CHART

		Skin color					
Hair color		X	X	X	X	X	X
		✓	✓	✓	✓	✓	X



APPLICATION



works with

MyIPL

Download on the
App Store

GET IT ON
Google Play

List of supported
devices

• iOS ≥ 8.0
• Android™ ≥ 4.4